

600V LARGE DIIPM Ver.6 Series APPLICATION NOTE

PSS**SA2F6

Table of contents

CHAPTER 1 INTRODUCTION	2
1.1 Target Applications	2
1.2 Product Line-up	2
1.3 Functions and Features	2
1.4 The Differences of Previous Series (600V Large DIIPM Ver.4) and This Series	3
CHAPTER 2 SPECIFICATIONS AND CHARACTERISTICS	4
2.1 Specifications	4
2.1.1 Maximum Ratings	4
2.1.2 Thermal Resistance	5
2.1.3 Electric Characteristics (Power Part)	6
2.1.4 Electric Characteristics (Control Part)	7
2.1.5 Recommended Operating Conditions	8
2.1.6 Mechanical Characteristics and Ratings	9
2.2 Protective Functions and Operating Sequence	10
2.2.1 Short Circuit Protection	10
2.2.2 Control Supply UV Protection	14
2.2.3 Temperature Output Function	16
2.3 Package Outlines	21
2.3.1 Outline Drawing	21
2.3.2 Power Chip Position	22
2.3.3 Marking Position	22
2.3.4 Terminal Description	23
2.4 Mounting Method	25
2.4.1 Electric Spacing	25
2.4.2 Mounting Method and Precautions	25
2.4.3 Soldering Conditions	26
CHAPTER 3 SYSTEM APPLICATION HIGHLIGHT	27
3.1 Application Guidance	27
3.1.1 System Connection	27
3.1.2 Interface Circuit (Direct Coupling Interface example)	28
3.1.3 Interface Circuit (Opto-coupler Isolated Interface)	29
3.1.4 Circuits of Signal Input terminals and Fo Terminal	30
3.1.5 Snubber Circuit	32
3.1.6 Influence of Wiring	33
3.1.7 Precaution for Wiring on PCB	34
3.1.8 SOA of DIIPM	35
3.1.9 SC SOA	36
3.1.10 Power Life Cycles	37
3.2 Power Loss and Thermal Dissipation Calculation	38
3.2.1 Power Loss Simulation	38
3.2.2 Temperature Rise Considerations and Calculation Example	40
3.3 Noise and ESD Withstand Capability	41
3.3.1 Evaluation Circuit of Noise Withstand Capability	41
3.3.2 Countermeasures and Precautions	41
3.3.3 Static Electricity Withstand Capability	42
CHAPTER 4 Bootstrap Circuit Operation	43
4.1 Bootstrap Circuit Operation	43
4.2 Bootstrap Supply Circuit Current at Switching State	44
4.3 Note for designing the bootstrap circuit	45
4.4 Initial charging in bootstrap circuit	46
CHAPTER 5 PACKAGE HANDLING	47
5.1 Packaging Specification	47
5.2 Handling Precautions	48