

<DIPIPM>

1200V LARGE DIPIPM Ver.4 Series APPLICATION NOTE

PS22A7x

Table of contents

CHAPTER 1 INTRODUCTION	2
1.1 Target Applications	2
1.2 Product Line-up	2
1.3 Functions and Features	2
1.4 The Differences of Previous Series (1200V Large DIPIPM PS2205*) and This Series	3
1.5 The Differences between 50A Rating PS22A79 and Others (PS22A72~PS22A78-E)	4
CHAPTER2 SPECIFICATIONS AND CHARACTERISTICS	5
2.1 Specifications	5
2.1.1 Maximum Ratings	5
2.1.2 Thermal Resistance	6
2.1.3 Electric Characteristics (Power Part)	6
2.1.4 Electric Characteristics (Control Part)	7
2.1.5 Recommended Operating Conditions	8
2.1.6 Mechanical Characteristics and Ratings	9
2.2 Protective Functions and Operating Sequence	10
2.2.1 Short Circuit Protection	10
2.2.2 Control Supply UV Protection	14
2.2.3 Temperature Output Function	15
2.3 Package Outlines	21
2.3.1 Outline Drawing	21
2.3.2 Power Chip Position	22
2.3.3 Marking Position	22
2.3.4 Terminal Description	23
2.4 Mounting Method	25
2.4.1 Electric Spacing	25
2.4.2 Mounting Method and Precautions	25
2.4.3 Soldering Conditions	26
CHAPTER3 SYSTEM APPLICATION HIGHLIGHT	27
3.1 Application Guidance	27
3.1.1 System Connection	27
3.1.2 Interface Circuit (Direct Coupling Interface example)	28
3.1.3 Interface Circuit (Opto-coupler Isolated Interface)	29
3.1.4 Circuits of Signal Input terminals and Fo Terminal	30
3.1.5 Snubber Circuit	32
3.1.6 Influence of Wiring	33
3.1.7 Precaution for Wiring on PCB	34
3.1.8 SOA of DIPIPM	35
3.1.9 SCSOA	36
3.1.10 Power Life Cycles	39
3.2 Power Loss and Thermal Dissipation Calculation	40
3.2.1 Power Loss Calculation	40
3.2.2 Temperature Rise Considerations and Calculation Example	42
3.3 Noise and ESD Withstand Capability	43
3.3.1 Evaluation Circuit of Noise Withstand Capability	43
3.3.2 Countermeasures and Precautions	43
3.3.3 Static Electricity Withstand Capability	44
CHAPTER 4 Bootstrap Circuit Operation	46
4.1 Bootstrap Circuit Operation	46
4.2 Bootstrap Supply Circuit Current at Switching State	47
4.3 Note for designing the bootstrap circuit	48
CHAPTER5 PACKAGE HANDLING	50
5.1 Packaging Specification	50
5.2 Handling Precautions	51