

< DIPIPM >

1200V Mini DIPIPM APPLICATION NOTE

PSS**S72FT

Table of contents

CHAPTER 1 INTRODUCTION	2
1.1 Features of 1200V Mini DIPIPM.....	2
1.2 Functions	3
1.3 Target Applications.....	4
1.4 Product Line-up.....	4
CHAPTER 2 SPECIFICATIONS AND CHARACTERISTICS	5
2.1 1200V Mini DIPIPM Specifications.....	5
2.1.1 Maximum Ratings.....	5
2.1.2 Thermal Resistance	7
2.1.4 Mechanical Characteristics and Ratings.....	10
2.2 Protective Functions and Operating Sequence.....	11
2.2.1 Short Circuit Protection	11
2.2.2 Control Supply UV Protection	13
2.2.3 Temperature output function V _{OT}	15
2.3 Package Outlines.....	20
2.3.1 Package outlines	20
2.3.2 Marking	21
The Lot number indicates production year, month, running number and country of origin.....	21
2.3.3 Terminal Description	22
2.4 Mounting Method	24
2.4.1 Electric Spacing.....	24
2.4.2 Mounting Method and Precautions	24
2.4.3 Soldering Conditions	25
CHAPTER 3 SYSTEM APPLICATION GUIDANCE.....	27
3.1 Application Guidance	27
3.1.1 System connection	27
3.1.2 Interface Circuit (Direct Coupling Interface example for using one shunt resistor).....	28
3.1.3 Interface Circuit (Example of Opto-coupler Isolated Interface)	29
3.1.4 External SC Protection Circuit with Using Three Shunt Resistors	30
3.1.5 Circuits of Signal Input Terminals and Fo Terminal.....	30
3.1.6 Snubber Circuit.....	32
3.1.7 Recommended Wiring Method around Shunt Resistor	33
3.1.8 Precaution for Wiring on PCB	35
3.1.9 Parallel operation of DIPIPM	36
3.1.10 SOA of 1200V Mini DIPIPM	36
3.1.11 SCSOA	37
3.1.12 Power Life Cycles.....	38
3.2 Power Loss and Thermal Dissipation Calculation	39
3.2.1 Power Loss Calculation	39
3.2.2 Temperature Rise Considerations and Calculation Example	41
3.3.1 Evaluation Circuit of Noise Withstand Capability	42
3.3.2 Countermeasures and Precautions	42
3.3.3 Static Electricity Withstand Capability	43
CHAPTER 4 Bootstrap Circuit Operation	44
4.1 Bootstrap Circuit Operation	44
4.2 Bootstrap Supply Circuit Current at Switching State	45
4.3 Note for designing the bootstrap circuit	46
4.4 Initial charging in bootstrap circuit.....	47
CHAPTER 5 PACKAGE HANDLING	48
5.1 Packaging Specification	48
5.2 Handling Precautions	49