

Table of Contents

CHAPTER 1 Super Mini DIP-IPM Ver.4 INTRODUCTION	3
1.1 Target Applications	3
1.2 Product Line-up	3
1.3 Functions and Features	3
1.4 The differences between previous series (PS2196X-XXX) and this series (PS2196X-4,-T)	5
CHAPTER 2 SPECIFICATIONS AND CHARACTERISTICS	6
2.1 Super Mini DIP-IPM Ver.4 Specifications	6
2.1.1 Maximum Ratings	6
2.1.2 Thermal Resistance	7
2.1.3 Electric Characteristics (Power Part)	7
2.1.4 Electric Characteristics (Control Part)	8
2.1.5 Recommended Operating Conditions	9
2.1.6 Mechanical Characteristics and Ratings	9
2.2 Protective Functions and Operating Sequence	10
2.2.1 Short Circuit Protection	10
2.2.2 Control Supply UV Protection	11
2.2.3 OT Protection	13
2.3 Package Outlines	14
2.3.1 Terminal frame change from previous series (PS2196X-XXX)	14
2.3.2 Short Pin Type Package Outline Drawing	15
2.3.3 Long Pin Type Package Outline Drawing	16
2.3.4 Zigzag Pin Type Package Outline Drawing	17
2.3.5 N-side Open Emitter Type Package Outline Drawing	18
2.3.6 Both Sides Zigzag Pin Type Package Outline Drawing	19
2.3.7 Laser Marking	20
2.3.8 Terminal Description	20
2.4 Mounting Method	22
2.4.1 Electric Spacing	22
2.4.2 Mounting Method and Precautions	22
CHAPTER 3 SYSTEM APPLICATION HIGHLIGHT	23
3.1 Application Guidance	23
3.1.1 System connection	23
3.1.2 Interface Circuit (Direct Coupling Interface example except for type ‘-S’)	24
3.1.3 Interface Circuit (Direct Coupling Interface Example for type ‘-S’)	25
3.1.4 Interface Circuit (Opto-coupler Isolated Interface)	26
3.1.5 Change into internal connection between V _{NO} and V _{NC} terminals	27
3.1.6 Circuits of Signal Input terminals and Fo Terminal	28
3.1.7 Snubber Circuit	29
3.1.8 Recommended Wiring method around Shunt Resistor	30
3.1.9 Precaution for wiring on PCB	31
3.1.10 SOA of Super Mini DIP-IPM Ver.4	32
3.1.11 Power Life Cycles	33
3.2 Power Loss and Thermal Dissipation Calculation	34
3.2.1 Power Loss Calculation	34
3.2.2 Temperature Rise Considerations and Calculation Example	36
3.3 Noise Withstand Capability	37
3.3.1 Evaluation Circuit	37
3.3.2 Countermeasures and Precautions	37
3.3.3 Static Electricity Withstand Capability	38
CHAPTER 4 KEY PARAMETERS SELECTING GUIDANCE	39
4.1 Determination of Shunt Resistance	39
4.2 Single Supply Drive Scheme	41
4.2.1 Bootstrap Capacitor Initial Charging	41
4.2.2 Charging and Discharging of the Bootstrap Capacitor During Inverter Operation	42
CHAPTER 5 INTERFACE DEMO BOARD	45
5.1 Super Mini DIP-IPM Ver.4 Interface Demo Board	45
5.2 Pattern Wiring	46
5.3 Circuit Schematic and Parts List	47
CHAPTER 6 PACKAGE HANDLING	49
6.1 Packaging Specification	49
6.2 Handling Precautions	50