

# Industrial Full SiC Power Module Application Note

## Index

<b>1. Introduction</b> .....	<b>3</b>
1.1. Features of Industrial Full SiC Power Modules .....	3
1.2. Structure .....	4
1.3. Configuration of the part number .....	5
1.4. Line up .....	5
1.5. Features of the SiC-SBD .....	6
1.5.1. Forward characteristics .....	6
1.5.2. Switching characteristics .....	6
1.6. Features of the SiC- MOSFET .....	7
1.6.1. On-voltage characteristics .....	7
1.6.2. Gate–source threshold voltage .....	8
1.6.3. MOSFET reverse conduction (channel conduction) .....	8
1.6.4. MOSFET reverse conduction (body diode) .....	9
1.6.5. Switching characteristics .....	9
<b>2. Glossary</b> .....	<b>10</b>
2.1. Common.....	10
2.2. Maximum Ratings .....	10
2.3. Temperature ratings .....	10
2.4. Thermal ratings and characteristics .....	10
2.5. Electric characteristics.....	11
2.6. Short-circuit current limiting circuit (RTC circuit) .....	11
<b>3. Product Label Information</b> .....	<b>12</b>
3.1. Label printing example.....	12
3.2. Lot number configuration .....	12
3.3. Two-dimensional barcode configuration.....	12
<b>4. Control circuit design</b> .....	<b>13</b>
4.1. Selection of gate resistance .....	13
4.2. Setting of gate voltage .....	14
4.2.1. Gate positive bias.....	14
4.2.2. Gate negative bias.....	15
4.3. Gate drive power supply .....	16
4.4. Dead time setting .....	16
4.5. Carrier frequency .....	17
4.6. Gate driver .....	17
<b>5. Short-circuit current limiting circuit (RTC circuit)</b> .....	<b>18</b>
5.1. Products equipped with RTC circuit.....	18
5.2. Principle of operation .....	18
5.3. Usage .....	20
5.4. How to calculate the short circuit detection delay time .....	21

<b>6. Current sense function</b>	<b>22</b>
6.1. How to use the sense terminal	22
6.2. How to manage when not using the sense terminal	22
<b>7. Power module implementation</b>	<b>23</b>
7.1. System Layout	23
7.2. Method of attaching the module to the heat sink	24
7.3. Thermally conductive (heat dissipating) grease application example	25
7.4. Installation to the main terminal	26
7.5. Mounting to control terminal	27
7.5.1. Connector type	27
7.5.2. Solder-pin type	27
7.6. Concept of thermal resistance	28
7.7. Example of thermocouple attachment	29
<b>8. How to use industrial full SiC Power modules</b>	<b>31</b>
8.1. Power module selection	31
8.1.1. Voltage rating	31
8.1.2. Current rating	31
8.2. Surge voltage suppression method	31
8.2.1. Reduction of main circuit wiring	31
8.2.2. Snubber circuit	32
8.3. Parallel operation	33
8.3.1. Current derating	33
8.3.2. Main circuit wiring	34
8.3.3. Gate drive circuit	35
<b>9. Power loss and heat dissipation design</b>	<b>36</b>
9.1. Power loss	36
9.1.1. Steady-state loss	37
9.1.2. Switching loss	38
9.1.3. Average power loss	39
9.2. Calculation of temperature rise	40
9.3. Heat sink selection	42
9.4. General precautions when applying to inverters	43
9.5. General precautions for thermal design	43
<b>10. Handling Precautions</b>	<b>44</b>
10.1. Handling Precautions	44
10.2. Flame Retardance	45
<b>11. Safety standard (UL Standard)</b>	<b>46</b>

Note) Numerical values and data described in this document are provided for reference purposes only.  
These values and data are not guaranteed.