

<Dual-In-Line Package Intelligent Power Module>

Super mini DIPIPM Ver.5 Series APPLICATION NOTE

PS219Bx -S/-ST/-AS/-AST/-CS/CST

Table of contents

CHAPTER 1 INTRODUCTION	2
1.1 Features of Super mini DIPIPM Ver.5	2
1.2 Functions	2
1.3 Target Applications	3
1.4 Product Line-up	4
1.5 The Differences between Previous Series and This Series (PS219B [*])	4
CHAPTER 2 SPECIFICATIONS AND CHARACTERISTICS	6
2.1 Super Mini DIPIPM Ver.5 Specifications	6
2.1.1 Maximum Ratings	6
2.1.2 Thermal Resistance	8
2.1.3 Electric Characteristics and Recommended Conditions	9
2.1.4 Mechanical Characteristics and Ratings	11
2.2 Protective Functions and Operating Sequence	12
2.2.1 Short Circuit Protection	12
2.2.2 Control Supply UV Protection	14
2.2.3 OT Protection (PS219B [*] -ST/AST/CST only)	16
2.2.4 Temperature output function V_{OT} (PS219B [*] -S/AS/CS only)	17
2.3 Package Outlines	22
2.3.1 Package outlines	22
2.3.2 Marking	25
2.3.3 Terminal Description	26
2.4 Mounting Method	28
2.4.1 Electric Spacing	28
2.4.2 Mounting Method and Precautions	28
2.4.3 Soldering Conditions	29
CHAPTER 3 SYSTEM APPLICATION GUIDANCE	30
3.1 Application Guidance	30
3.1.1 System connection	30
3.1.2 Interface Circuit (Direct Coupling Interface example for using one shunt resistor)	31
3.1.3 Interface Circuit (Example of Opto-coupler Isolated Interface)	32
3.1.4 External SC Protection Circuit with Using Three Shunt Resistors	33
3.1.5 Circuits of Signal Input Terminals and Fo Terminal	33
3.1.6 Snubber Circuit	35
3.1.7 Recommended Wiring Method around Shunt Resistor	35
3.1.8 Precaution for Wiring on PCB	37
3.1.9 Parallel operation of DIPIPM	38
3.1.10 SOA of DIP Ver.5	38
3.1.11 SCSOA	39
3.1.12 Power Life Cycles	40
3.2 Power Loss and Thermal Dissipation Calculation	41
3.2.1 Power Loss Calculation	41
3.2.2 Temperature Rise Considerations and Calculation Example	43
3.3 Noise and ESD Withstand Capability	44
3.3.1 Evaluation Circuit of Noise Withstand Capability	44
3.3.2 Countermeasures and Precautions	44
3.3.3 Static Electricity Withstand Capability	45
CHAPTER 4 Bootstrap Circuit Operation	46
4.1 Bootstrap Circuit Operation	46
4.2 Bootstrap Supply Circuit Current at Switching State	47
4.3 Note for designing the bootstrap circuit	48
4.4 Initial charging in bootstrap circuit	49
CHAPTER 5 PACKAGE HANDLING	50
5.1 Packaging Specification	50
5.2 Handling Precautions	51