

Super mini DIIPM Ver.7 Series APPLICATION NOTE

PSSxxS93x6-AG

Table of contents

| | |
|--|----|
| CHAPTER 1 INTRODUCTION | 2 |
| 1.1 Features of Super mini DIIPM Ver.7 | 2 |
| 1.2 Functions | 2 |
| 1.3 Target Applications | 3 |
| 1.4 Product Line-up | 4 |
| 1.5 The Differences between Previous Series and This Series (PSS**S93*6) | 4 |
| CHAPTER 2 SPECIFICATIONS AND CHARACTERISTICS | 7 |
| 2.1 Super Mini DIIPM Ver.7 Specifications | 7 |
| 2.1.1 Maximum Ratings | 7 |
| 2.1.2 Thermal Resistance | 9 |
| 2.1.3 Electric Characteristics and Recommended Conditions | 10 |
| 2.1.4 Mechanical Characteristics and Ratings | 13 |
| 2.2 Protective Functions and Operating Sequence | 14 |
| 2.2.1 Short Circuit Protection | 14 |
| 2.2.2 Control Supply UV Protection | 16 |
| 2.2.3 OT Protection (PSS**S93E6-* only) | 18 |
| 2.2.4 Temperature output function V_{OT} (PSS**S93F6-* only) | 19 |
| 2.3 Package Outlines | 24 |
| 2.3.1 Package outlines | 24 |
| 2.3.2 Marking | 25 |
| 2.3.3 Terminal Description | 26 |
| 2.4 Mounting Method | 28 |
| 2.4.1 Electric Spacing | 28 |
| 2.4.2 Mounting Method and Precautions | 28 |
| 2.4.3 Soldering Conditions | 29 |
| CHAPTER 3 SYSTEM APPLICATION GUIDANCE | 30 |
| 3.1 Application Guidance | 30 |
| 3.1.1 System connection | 30 |
| 3.1.2 Interface Circuit (Direct Coupling Interface example for using one shunt resistor) | 31 |
| 3.1.3 Interface Circuit (Example of Optocoupler Isolated Interface) | 32 |
| 3.1.4 External SC Protection Circuit with Using Three Shunt Resistors | 33 |
| 3.1.5 Circuits of Signal Input Terminals and Fo Terminal | 33 |
| 3.1.6 Snubber Circuit | 35 |
| 3.1.7 Recommended Wiring Method around Shunt Resistor | 35 |
| 3.1.8 Precaution for Wiring on PCB | 37 |
| 3.1.9 Parallel operation of DIIPM | 38 |
| 3.1.10 SOA of DIIPM Ver.7 | 38 |
| 3.1.11 SCSOA | 39 |
| 3.1.12 Power Life Cycles | 41 |
| 3.2 Power Loss and Thermal Dissipation Calculation | 42 |
| 3.2.1 Power Loss Calculation | 42 |
| 3.2.2 Temperature Rise Considerations and Calculation Example | 44 |
| 3.2.3 Installation of thermocouple | 45 |
| 3.3 Noise and ESD Withstand Capability | 46 |
| 3.3.1 Evaluation Circuit of Noise Withstand Capability | 46 |
| 3.3.2 Countermeasures and Precautions | 46 |
| 3.3.3 Static Electricity Withstand Capability | 47 |
| CHAPTER 4 Bootstrap Circuit Operation | 48 |
| 4.1 Bootstrap Circuit Operation | 48 |
| 4.2 Bootstrap Supply Circuit Current at Switching State | 49 |
| 4.3 Note for designing the bootstrap circuit | 50 |
| 4.4 Initial charging in bootstrap circuit | 52 |
| CHAPTER 5 Interface Demo Board | 53 |
| 5.1 Super mini DIIPM Ver.7 Interface Demo Board | 53 |
| 5.2 Circuit Schematic, Parts List and Board pattern, | 55 |
| CHAPTER 6 PACKAGE HANDLING | 57 |
| 6.1 Packaging Specification | 57 |
| 6.2 Handling Precautions | 58 |